



## Trailer

By Chance Lineman Tools & Equipment  
Catalog # [C4050300](#)

Sturdy construction Aluminum (0.30" thick) skin delivers advantages of rustproof for long service life and light weight for towing ease. White is exterior-finish color. Plywood interior-wall linings and floor add durability for linework conditions. Interior walls are vinyl coated white to enhance illumination. Running gear, brakes and towing group are load-rated for road-worthy dependability. Electrical components meet applicable standards. The upright workspace and all-weather shelter of these units makes them line-crew favorites. Easy-handling standard- trailer lengths of 16 and 20 feet provide adequate capacity for most hot-line tool sets. Non-stock trailer sizes available by special order are listed below. Towing-hitch choices include 3" pintle-eye or optional 2.3125" ball-type. Be sure to specify hitch type when ordering. A full range of factory-installed optional equipment is listed below and on the next page. Any accessory selected must specified as a separate line item when ordering.

### General

Style 20' (6 m) Walk-In

### Dimensions

Weight 2450 lb



\*Representative Image

### Product Assets

[Catalogs - Tools Repair & Storage \(2500\)](#)  
[Literature - Walk-In Tool Trailers \(BR09108E\)](#)  
[Technical Solutions - CH-C4050300-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-C4050300-SPEC-EN | REV 1/2024