

Class 3, Short-Lip Flexible Line Hose, 4.5 ft

By Chance Lineman Tools & Equipment
Catalog # [C4060308](#)



Much lighter in weight than other flexible dielectric cover-up, Line Hose helps protect workers from accidental contact with conductors. In accordance with ASTM D 1050-90, ozone/corona resistant thermoplastic elastomer offers excellent performance properties. It does not absorb water. Easy to handle and place. The outer lip peels back with ease to open and start onto a conductor from either end. With a push at the other end, the full length slides on as the lips zip closed around the conductor. To remove each piece, open one end and strip the remainder off the conductor.

Features

- High visibility orange color
- Type III ozone resistant material
- Class 3
- Maximum use voltage of 26.5kV phase-to-phase
- 100% electrically tested and visually inspected per ASTM D1050
- Date stamped
- Coupler, one end
- Style B

General

Catalog Number	C4060308
Color	Orange
Style	Coupler On One End
Type	III
UPC	096359020868

Dimensions

Diameter	1.5 in
----------	--------

Length	54 in
Length Metric	137 cm
Weight	5.8 lb
WeightMetric	2.6 kg

Electrical Ratings

Voltage - Maximum	26.5 kV
Voltage Rating	Class 3 V

Conductor Related

Conductor Size	1.5" diameter
----------------	---------------

Logistics

Pallet Quantity	60
-----------------	----

Product Assets

[Catalogs - Cover-Up Equipment](#)
[Literature - Cover-Up Care](#)
[Specifications - C4060308](#)