

Class 4, Extended-Lip Flexible Line Hose Coupler

By Chance Lineman Tools & Equipment
Catalog # C4060340



COUPLER, CLASS #4, As much as 25 percent lighter in weight than other Class flexible cover-up, Line Hose helps protect workers from accidental contact with conductors. In accordance with ASTM D 1050-90, ozone/corona-resistant thermoplastic elastomer offers excellent performance properties. To retain high-visibility orange color, the special formulation exhibits superior resistance to long-term aging/checking. It does not absorb water.

Features

- Class 4 line hose coupler
- Type III ozone resistant material
- Also works with Class 3 line hose

General

Catalog Number	C4060340
Color - Jumper Insulation	Orange
EU RoHS Indicator	No
Style	Coupler
Type	III
UPC	096359021018

Dimensions

Diameter	1.5 in
----------	--------

Length	10.5 ft
Length Metric	3.2 m
Weight	2 lb
Weight Metric	0.9 kg

Electrical Ratings

Voltage - Maximum	36 kV
Voltage Rating	Class 4 V

Logistics

Pallet Quantity	216
-----------------	-----

Product Assets

[Literature - Cover-Up Care Specifications - C4060340](#)