



Class 4, Extended-Lip Flexible Line Hose, 3 ft

By Chance Lineman Tools & Equipment
Catalog # [C4060341](#)

LINE HOSE, 1-1/2"X36" CL.3 & 4, As much as 25 percent lighter in weight than other Class flexible cover-up, Line Hose helps protect workers from accidental contact with conductors. In accordance with ASTM D 1050-90, ozone/corona-resistant thermoplastic elastomer offers excellent performance properties. To retain high-visibility orange color, the special formulation exhibits superior resistance to long-term aging/checking. It does not absorb water.

Features

- High visibility orange color
- Type III ozone resistant material
- Class 4
- Maximum use voltage of 36.0kV phase-to-phase
- 100% electrically tested and visually inspected per ASTM D1050
- Date stamped
- Plain, both ends
- Style C

General

Catalog Number	C4060341
Color	Orange
EU RoHS Indicator	No
Style	Straight on both ends
Type	III
UPC	096359021025

Dimensions

Diameter	1.5 in
Length	36 in



Length Metric	91 cm
Weight	3.9 lb
Weight Metric	1.7 kg

Electrical Ratings

Voltage - Maximum	36 kV
Voltage Rating	Class 4 V

Conductor Related

Conductor Size	1.5" diameter
----------------	---------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	90
-----------------	----

Product Assets

- [Catalogs - Cover-Up Equipment](#)
- [Literature - Cover-Up Care](#)
- [Specifications - C4060341](#)



A Hubbell brand