

# Class 4, Extended-Lip Flexible Line Hose, 4.5 ft

By Chance Lineman Tools & Equipment  
Catalog # [C4060342](#)



LINE HOSE, 1-1/2"X54" CL.3 & 4, As much as 25 percent lighter in weight than other Class flexible cover-up, Line Hose helps protect workers from accidental contact with conductors. In accordance with ASTM D 1050-90, ozone/corona-resistant thermoplastic elastomer offers excellent performance properties. To retain high-visibility orange color, the special formulation exhibits superior resistance to long-term aging/checking. It does not absorb water.

## Features

- High visibility orange color
- Type III ozone resistant material
- Class 4
- Maximum use voltage of 36.0kV phase-to-phase
- 100% electrically tested and visually inspected per ASTM D1050
- Date stamped
- Plain, both ends
- Style C

## General

Catalog Number	C4060342
Color	Orange
EU RoHS Indicator	No
Style	Straight on both ends
Type	III
UPC	096359021032

## Dimensions

Diameter	1.5 in
Length	54 in

Length Metric	137 cm
Weight	7.9 lb
Weight Metric	3.5 kg

## Electrical Ratings

Voltage - Maximum	36 kV
Voltage Rating	Class 4 V

## Conductor Related

Conductor Size	1.5" diameter
----------------	---------------

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

## Logistics

Pallet Quantity	90
-----------------	----

## Product Assets

[Catalogs - Cover-Up Equipment](#)  
[Literature - Cover-Up Care](#)  
[Specifications - C4060342](#)