

Ground Clamp - Tower III-B-5

By Chance Lineman Tools & Equipment
Catalog # C6000085

Tower Clamp with T-handle, serrated jaw, 4.00" Jaw Opening,
ASTM Grade 5



*Representative Image

Features

- Aluminum body and retainer
- Bronze scrubber-type contact pads
- Bronze T-handle with fine threads
- Bronze pressure-type terminal

General

Catalog Number	C6000085
Eye Screw/T-Handle	N/A
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Handle Type	T-Handle
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359023265

Dimensions

Jaw Opening Size - Maximum	4 in
Jaw Opening Size - Minimum	2 in
Weight	3.43 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications And Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Pallet Quantity	320
-----------------	-----

Product Assets

[Catalogs - Grounding Equipment](#)
[Sales Drawings - Tower Angle Ground Clamp](#)
[Specifications - C6000085](#)