

Ground Cluster Bar 11" for Pole Mounting, Grade 5H

By Chance Lineman Tools & Equipment

Catalog # [C6000152](#)



Compact 11" copper bar (5/8" diameter) accepts C-type or duckbill grounding clamps for equipotential grounding. Adjustable wheel binder and 36" chain for wood-pole applications. (Longer chain lengths available.) Accepts plain ferrules on #2 to 4/0 grounding cable. NOTE: The use of the plain ferrule lead IS NOT rated for 5H. The use of it will reduce the ASTM F855 rating from 5H to whatever the cable size dictates.

Features

- Compact 11" copper bar (5/8" diameter) accepts C-type or duckbill grounding clamps for equipotential grounding
- Adjustable wheel binder and 36" chain for wood-pole applications (Longer chain lengths available)
- Accepts plain ferrules on #2 to 4/0 grounding cable
- NOTE: The use of the plain ferrule lead IS NOT rated for 5H
- The use of a plain ferrule will reduce the ASTM F855 rating from 5H to whatever the cable size dictates

General

Catalog Number	C6000152
Mounting Type	Pole Mounted w/ 1 Terminal
UPC	096359023319

Dimensions

Dimensions	13.25 in x 19.38 in x 5.33 in
Height	5.33 in
Length	13.25 in
Weight	12.74 lb
Width	19.38 in

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Fault Current - ASTM Grade	5

Logistics

Pallet Quantity	48
-----------------	----

Product Assets

[Catalogs - Grounding Equipment](#)
[Sales Drawings - SA600-0152](#)
[Specifications - C6000152](#)
[Video - CHANCE Temporary Protective Grounding](#)
[Video - CHANCE Temporary Protective Grounding](#)