

Ground Clamp, C-Type, Mounted 6', Type II-Class B-Grade 5, 2.0" Jaw Opening



By Chance Lineman Tools & Equipment
 Catalog # [C6000386](#)

Ground Clamp, C-Type, Mounted 6', Type II-Class B-Grade 5, 2.0"
 Jaw Opening

Features

- C-Type Mounted Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 2" O.D. Bus
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type II, Class B, Grade 5
- Jaws Serrated
- Ferrule Plain-Plug

General

EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Hotstick
Jaw Type	Serrated Jaws
Material	Aluminum
Mounting Type	Pole Mounted
Terminal Connection Type	Pressure
Torque Rating	
UPC	096359023395

Dimensions

Jaw Opening Size - Maximum	2 in
Jaw Opening Size - Minimum	.162 in
Length	6 in
Weight	8.33 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications And Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Product Assets

[Catalogs - Grounding Equipment](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C6000386-SPEC-EN | REV 6/2024