

Mounted Bus Bar Ground Clamp 9', Type II-Class A-Grade 5 or 6 (twin- ground cables), 6.625" Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # [C6000618](#)

Mounted Bus Bar Ground Clamp 9', Type II-Class A-Grade 5 or 6
(twin-ground cables), 6.625" Jaw Opening

Features

- Mounted Bus-Bar Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles
- Main Line Range Max. 6-5/8" Angles
- Main Line Range Min. 4-1/2" O.D. Bus
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type II, Class A, Grade 5 or Grade 6
- Jaws Smooth
- Ferrule Plain-Plug

General

EU RoHS Indicator	No
Eye Screw/T-Handle	N/A
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Handle Type	Hotstick
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Dual Pressure
UPC	096359023562

Dimensions

Jaw Opening Size - Maximum	6.375 in
Jaw Opening Size - Minimum	3.5 in
Length	9 in
Weight	11.76 lb



Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications And Compliance

Fault Current - ASTM Grade	ASTM Grade 6
----------------------------	--------------

Product Assets

[Catalogs - Grounding Equipment](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C6000618-SPEC-EN | REV 6/2024