



## 6ft. #2 Chisel-Point Temporary Grounding Set for URD Cable

By Chance Lineman Tools & Equipment  
Catalog # [C6001625](#)

6ft. #2 Chisel-Point Temporary Grounding Set for URD Cable



### Features

- For temporary grounding of underground distribution cable with jacket over concentric neutral
- Used to confirm the cable that will be worked on is de-energized
- Chisel-point ensures contact with center conductor
- Chisel-point clamp main-line capacity is 1-1/2in.
- C-clamp in chisel sets fits conductors from #6 (0.162in.) to 2.0in. O.D. bs
- Each set includes 6ft. of #2 copper clear-jacket ground cable and ferrules, a chisel clamp and C-clamp

### General

EU RoHS Indicator No  
UPC 096359023708

### Dimensions

Jaw Opening Size - Maximum .998 in  
Jaw Opening Size - Minimum .162 in  
Weight 7.84 lb

### Logistics

Pallet Quantity 52

### Product Assets

[Catalogs - Grounding Equipment](#)  
[Video - CHANCE Temporary Protective Grounding](#)