

## Penetrator Clamp for U.R.D. Cable - Chisel

By Chance Lineman Tools & Equipment  
Catalog # [C6001626](#)

For temporary grounding of underground distribution cable with jacket over concentric neutral, specials help ensure contact with center conductor. Chisel-point main-line capacity is 112". C-Type in Chisel Sets fits conductors from #6 (0.162") to 636 kcmil ACSR (0.998").



### General

EU RoHS Indicator	No
Eye Screw/T-Handle	N/A
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Handle Type	Eyescrew
Jaw Type	Chisel Point
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359023715

### Dimensions

Jaw Opening Size - Maximum	.998 in
Jaw Opening Size - Minimum	.162 in
Weight	1.725 lb

### Electrical Ratings

Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

### Logistics

Carton Quantity	15
Pallet Quantity	450

### Product Assets

[Catalogs - Grounding Equipment](#)