



# Ground Clamp, Flat Face, Type I-Class B-Grade 3, 1.5" Jaw Opening

By Chance Lineman Tools & Equipment  
Catalog # C6001735

Ground Clamp, Flat Face, Type I-Class B-Grade 3, 1.5" Jaw Opening



\*Representative Image

## Features

- Tower & Flat-Face Ground Clamp
- Continuous Current 400A
- Fault Current 27kA for 15 cycles or 20kA for 30 cycles
- Main Line Range Max. 1.5" Angles or 1.5" Flat
- Main Line Range Min. 1/8"
- Jumper Range Max. 2/0 Grd. Cable w/ Threaded Stud
- Jumper Range Min. #2 Grd. Cable w/ Threaded Stud
- ASTM Type I, Class B, Grade 3
- Jaws Serrated
- Ferrule Threaded

## General

EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
UPC	096359023883

## Dimensions

Jaw Opening Size - Maximum	1.5 in
Jaw Opening Size - Minimum	.125 in
Weight	1.48 lb

## Electrical Ratings

Current Rating	300 A
Fault Current - 15 Cycles	27000 A
Fault Current - 30 Cycles	20000 A
Grounding Wire Capacity Maximum	2/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

## Certifications and Compliance

Fault Current - ASTM Grade	ASTM Grade 3
----------------------------	--------------

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-C6001735-SPEC-EN | REV 1/2024