

Temporary Protective Grounding Simulator Kit

By Chance Lineman Tools & Equipment
Catalog # C6001950



Temporary Protective Grounding Simulator Kit

Features

- Demonstrates principles for temporary grounding practices
- Portable instruction aid provides working model of three-phase system circuit
- Powered by a step-down transformer
- Plugs into a 110-volt 60-cycle household source
- Special light/buzzer unit simulates line worker in maintenance on de-energized line
- Insulated wires with alligator clip at each ends serve as grounding cable and clamp sets (10 included)
- Miniature grounding cluster bar is included for pole mounting

General

EU RoHS Indicator No
UPC 096359023999

Dimensions

Dimensions 34.5 in x 7 in x 12.38 in
Height 12.38 in
Length 34.5 in
Weight 47.04 lb
Width 7 in

Product Assets

[Catalogs - Grounding Equipment](#)
[Installation Manuals - CHANCE Grounding Simulator Kit](#)
[Assembly Instructions](#)
[Literature - Encyclopedia of Grounding](#)
[Video - CHANCE Temporary Protective Grounding](#)
[Video - CHANCE Temporary Protective Grounding](#)