

Ground Clamp w/ eye screw for Switch Blade switch

By Chance Lineman Tools & Equipment
Catalog # [C6002145](#)

Bronze attaches temporary ground to open switch during deenergized maintenance. Designed to help keep ground lead away from energized switch jaw, is shaped to fit specifically the blades of such switches as Type M3 Disconnect.'s drilled terminal accepts threaded-stud ferrules on grounding cable from #2 through 4/0. It also accepts threaded L-Stud Terminal (3/4" diameter bronze) for use with conventional groundclamp cable sets.



General

Bolt Installation Torque
(Recommended)

EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Material	Bronze
Terminal Connection Type	Drilled Terminal
UPC	096359024200

Dimensions

Weight 1.96 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity	4/0 Cable w/ Threaded
Maximum	Terminal
Grounding Wire Capacity	#2 Cable w/ Threaded Terminal
Minimum	

Certifications And Compliance

Fault Current - ASTM Grade ASTM Grade 5

Logistics

Pallet Quantity 576

Product Assets

[Catalogs - Grounding Equipment](#)



A Hubbell brand