

Ground Clamp, Flat Face, Type III-Class B-Grade 5, 1.5" Jaw Opening

By Chance Lineman Tools & Equipment

Catalog # [C6002231](#)

Ground Clamp, Flat Face, Type III-Class B-Grade 5, 1.5" Jaw Opening

Features

- Tower & Flat-Face Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 1.5" Angles or 1.5" Flat
- Main Line Range Min. 1/8"
- Jumper Range Max. 4/0 Grd. Cable w/ Threaded Stud
- Jumper Range Min. #2 Grd. Cable w/ Threaded Stud
- ASTM Type III, Class B, Grade 5
- Jaws Serrated
- Ferrule Threaded

General

| | |
|-------------------------------------|----------------|
| Catalog Number | C6002231 |
| Eye Screw/T-Handle | 250 in-lb |
| Installation Torque (in-lb) | |
| Ferrule Installation Torque (in-lb) | 250 in-lb |
| Handle Type | T-Handle |
| Jaw Type | Serrated Jaws |
| Material | Bronze |
| Terminal Connection Type | 5/8"-11 Thread |
| Thread Size | 5/8-11 UNC |
| Thread Type | Threaded |
| Torque Rating | 250 in-lbs |
| UPC | 096359024323 |

Dimensions



| | |
|----------------------------|----------|
| Jaw Opening Size - Maximum | 1.5 in |
| Jaw Opening Size - Minimum | .125 in |
| Weight | 2.666 lb |

Electrical Ratings

| | |
|---------------------------------|--------------------------------|
| Current Rating | 400 A |
| Fault Current - 15 Cycles | 43000 A |
| Fault Current - 30 Cycles | 30000 A |
| Grounding Wire Capacity Maximum | 4/0 Cable w/ Threaded Terminal |
| Grounding Wire Capacity Minimum | #2 Cable w/ Threaded Terminal |

Certifications And Compliance

| | |
|----------------------------|---|
| Buy America(n) Qualified | TAA Compliant (All status valid till December 2024) |
| Fault Current - ASTM Grade | ASTM Grade 5 |

Logistics

| | |
|-----------------|-----|
| Pallet Quantity | 720 |
|-----------------|-----|

Product Assets

[Catalogs - Grounding Equipment](#)
[Sales Drawings - C6002231 Flat Face Clamp T Handle](#)
[Sales Drawings - SA600-2231](#)
[Specifications - C6002231](#)