



Ground Clamp, C-Type, Type I- Class A-ASTM Grade 5H, IEC Rating 35kA (15 Cycles), 2.0" Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # C6002255

Ground Clamp, C-Type, Type I-Class A-ASTM Grade 5H, IEC
Rating 35kA (15 Cycles), 2.0" Jaw Opening



Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current 47kA, X/R=30
- Main Line Range 2" O.D. Bus
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 5H
- IEC Rating 35kA (15 Cycles)
- Jaws Smooth
- Ferrule Threaded - Unshrouded Only

General

Eye Screw/T-Handle Installation Torque (in-lb)	250 in-lb
Ferrule Installation Torque (in- lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
UPC	096359024354

Dimensions

Jaw Opening Size - Maximum	2 in
Jaw Opening Size - Minimum	.162 in
Weight	1.96 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	47000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications And Compliance

Fault Current - ASTM Grade	ASTM Grade 5H
----------------------------	---------------

Logistics

Pallet Quantity	480
-----------------	-----

Product Assets

[Catalogs - Grounding Equipment](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-C6002255-SPEC-EN | REV 6/2024