

Grounding Ferrule - Shrouded Threaded - 1/0 Copper

By Chance Lineman Tools & Equipment
Catalog # [C6002623](#)



Shrouded threaded copper ferrule 1/0

*Representative Image

Features

- GROUNDING FERRULE-THREADED-SHROUDED- 1/0 CU
- Shrouded ferrules overlap onto the grounding cable jacket for stress relief to the terminal
- Two crimps secure the ferrule against the bare strands and one crimp applies on the jacket
- Available either factory-installed in pairs on any cable length specified or as separate individual units
- The ferrules install simply with a hydraulic crimping tool
- Complete illustrated installation instructions come with the ferrules and include a table for the crimping die sizes to use

General

Die Size - Section A	U165
Die Size - Section B	U168
Material	Copper
Shrouded?	Shrouded
Terminal Connection Type	Threaded or Drilled
Thread Size	5/8-11 UNC
UPC	096359233169

Dimensions

Weight	0.314 lb
--------	----------

Electrical Ratings

Current Rating	250 A
Fault Current - 15 Cycles	21000 A
Fault Current - 30 Cycles	15000 A

Conductor Related

Conductor Size	1/0 AWG
----------------	---------

Product Assets

[Catalogs - Grounding Equipment](#)

[Sales Drawings - SA600-2618](#)

[Video - CHANCE Temporary Protective Grounding](#)



A Hubbell brand