

Grounding Ferrule - Shrouded Threaded - 2/0 Copper

By Chance Lineman Tools & Equipment
Catalog # [C6002624](#)



Shrouded threaded copper ferrule 2/0

*Representative Image

Features

- GROUNDING FERRULE-THREADED-SHROUDED- 2/0 CU
- Shrouded ferrules overlap onto the grounding cable jacket for stress relief to the terminal
- Two crimps secure the ferrule against the bare strands and one crimp applies on the jacket
- Available either factory-installed in pairs on any cable length specified or as separate individual units
- The ferrules install simply with a hydraulic crimping tool
- Complete illustrated installation instructions come with the ferrules and include a table for the crimping die sizes to use

General

Catalog Number	C6002624
Die Size - Section A	U165
Die Size - Section B	U-L
Material	Copper
Shrouded?	Shrouded
Terminal Connection Type	Threaded or Drilled

Thread Size	5/8-11 UNC
UPC	096359233176

Dimensions

Weight	0.461 lb
--------	----------

Electrical Ratings

Current Rating	300 A
Fault Current - 15 Cycles	27000 A
Fault Current - 30 Cycles	20000 A

Conductor Related

Conductor Size	2/0 AWG
----------------	---------

Product Assets

- [Catalogs - Grounding Equipment](#)
- [Sales Drawings - SA600-2618](#)
- [Specifications - C6002624](#)
- [Video - CHANCE Temporary Protective Grounding](#)