

Grounding Ferrule - Shrouded Plain - 1/0 Copper

By Chance Lineman Tools & Equipment
Catalog # [C6002631](#)



Shrouded plain plug copper ferrule 1/0

Features

- GROUNDING FERRULE-PLAIN-SHROUDED- 1/0 CU
- Shrouded ferrules overlap onto the grounding cable jacket for stress relief to the terminal
- Two crimps secure the ferrule against the bare strands and one crimp applies on the jacket
- Available either factory-installed in pairs on any cable length specified or as separate individual units
- The ferrules install simply with a hydraulic crimping tool
- Complete illustrated installation instructions come with the ferrules and include a table for the crimping die sizes to use

General

Die Size - Section A	U165
Die Size - Section B	U168
Material	Copper
Power Supply	
Shrouded?	Shrouded
Style	
Swivel Top?	
Terminal Connection Type	Pressure or Plain
Thread Size	
Type	
UPC	096359233244

Dimensions

Jaw Width	
Weight	0.539 lb

Electrical Ratings

Amperage - Display Range	
Current Rating	250 A
Fault Current - 15 Cycles	21000 A
Fault Current - 30 Cycles	15000 A
Withstand Voltage	

Conductor Related

Conductor Size	1/0 AWG
Strands	

Product Assets

- [Catalogs - Grounding Equipment](#)
- [Sales Drawings - SA600-2630](#)
- [Video - CHANCE Temporary Protective Grounding](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C6002631-SPEC-EN | REV 6/2024