



34.5kV Insulated Bypass Jumper 16 ft (4.8 m)

By Chance Lineman Tools & Equipment

Catalog # [C6010037](#)



BY-PASS JUMPER-34.5kV-10 ft POLE-16 ft OAL, 34.5kV rating between the rubber guards. A solid aluminum rod is epoxi-sealed inside a polypropylene tube which is silicone-sealed inside a 1.5 in Hotstick handle. Brass couplings are threaded onto the end of the solid rod, pinned and three feet of 4/0, clear-jacketed grounding cable is threaded into the coupling. Current capacity is 400 amps.

Features

or head

General

Catalog Number	C6010037
EU RoHS Indicator	No
Thread Size	5/8" - 11 UNC
UPC	096359024507

Dimensions

Diameter	1.5 in
Length	16 ft
Weight	21.3 lb
WeightMetric	9.6 kg

Electrical Ratings

Amperage Rating	400
Current Rating	400 A
Voltage - Maximum	34.5 kV
Voltage Rating	34.5 kV

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Product Assets

[Catalogs - Jumpers & Load Pickup Tools](#)
[Sales Drawings - SA_601-0036](#)
[Specifications - C6010037](#)



A Hubbell brand