

## 15kV Rubber Glove Jumper Set 12 ft (3.6 m) #2 with Orange Clamps

By Chance Lineman Tools & Equipment  
Catalog # [C6010163](#)



15kV 12 ft #2 Rubber Glove Jumper Set, 15kV Orange Clamps

### Features

- Designed and tested to ASTM F2321
- Complete set rated to 15kV
- Includes G4758 15kV Rubber Glove Jumper Clamps and 12ft of S10043 #2 15kV Jumper Cable
- Continuous current rating of 200 amps
- Conductor range of #6 CU to 795 ACSR
- Used for bypassing work areas when equipment is under repair, upgrading lines, and making temporary or emergency repairs
- Clamps have 5-5/8" below the handguard
- Adequate rubber gloves must be worn when installing or removing jumper clamps

### General

EU RoHS Indicator	No
Style	Rubber Glove Applied
UPC	096359024576

### Dimensions

Length	12 ft
Length - Jumper	144 in
Weight	10.7 lb
WeightMetric	4.8 kg

### Electrical Ratings

Amperage Rating	200
Current Rating	200 A
Voltage - Maximum	15 kV
Voltage Rating	15 kV

### Conductor Related

Conductor Diameter (Main) - Maximum	0.7
Conductor Diameter (Main) - Minimum	0.1
Conductor Size	#2 AWG

### Logistics

Pallet Quantity 24

### Product Assets

