



25kV Rubber Glove Jumper Set 12 ft (3.6 m) 2/0 with Orange Clamps

By Chance Lineman Tools & Equipment
Catalog # [C6010270](#)



25kV 12 ft 2/0 Rubber Glove Jumper Set, Orange Clamps

Features

- Designed and tested to ASTM F2321
- Complete set rated to 25kV
- Includes G4765 25kV Rubber Glove Jumper Clamps and 12ft of S11273 2/0 15kV Jumper Cable
- Continuous current rating of 300 amps
- Conductor range of #6 CU to 795 ACSR
- Used for bypassing work areas when equipment is under repair, upgrading lines, and making temporary or emergency repairs
- Clamps have 7-1/2" below the handguard
- Adequate rubber gloves must be worn when installing or removing jumper clamps

General

Catalog Number	C6010270
EU RoHS Indicator	No
Style	Rubber Glove Applied
UPC	096359024835

Dimensions

Length	12 ft
Length - Jumper	144 in
Weight	19.6 lb

WeightMetric	8.8 kg
--------------	--------

Electrical Ratings

Amperage Rating	300
Current Rating	300 A
Voltage - Maximum	25 kV
Voltage Rating	25 kV

Conductor Related

Conductor Diameter (Main) - Maximum	0.8 in
Conductor Diameter (Main) - Minimum	0.1 in
Conductor Size	2/0 AWG

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	24
-----------------	----

Product Assets

[Catalogs - Jumpers & Load Pickup Tools](#)
[Specifications - C6010270](#)



A Hubbell brand