



Pole Clamp for Adjustable Strain Poles

By Chance Lineman Tools & Equipment
Catalog # [E4010138P](#)



Replacement Pole Clamp for Adjustable Strain Pole.

Features

- 2" Adjustable Pole Clamp

General

EU RoHS Indicator	No
Style	Accessories
UPC	096359083931

Dimensions

Length	2 in
Length Metric	5.1 mm
Weight	2.0 lb
WeightMetric	0.9 kg

Product Assets

[Literature - Transmission Project Tools and Equipment Checklist \(CENT_LTE_FRM_EN_00082\)](#)

Related Products

- [C4012147 - Adjustable Strain Pole, 10 ft \(3.0 m\), 5 Pins](#)
- [C4012146 - Adjustable Strain Pole, 8 ft \(2.4 m\), 5 Pins](#)
- [C4012145 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012144 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012149 - Adjustable Strain Pole, 18 ft \(5.4 m\), 5 Pins](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-E4010138P-SPEC-EN | REV 1/2024