



# Steel Through Pin for Adjustable Strain Poles

By Chance Lineman Tools & Equipment  
Catalog # [E4011510P](#)



LOCKING PIN FOR STRAIN POLE - .75 X 3.5, Replacement Steel Through Pin.

## Features

- Steel Through Pin

## General

EU RoHS Indicator	No
Style	Accessories
UPC	096359084150

## Dimensions

Length	3.5 in
Length Metric	8.9 mm
Weight	0.6 lb
WeightMetric	0.2 kg

## Product Assets

[Literature - Transmission Project Tools and Equipment Checklist \(CENT\\_LTE\\_FRM\\_EN\\_00082\)](#)

## Related Products

- [C4012145 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012146 - Adjustable Strain Pole, 8 ft \(2.4 m\), 5 Pins](#)
- [C4012144 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012147 - Adjustable Strain Pole, 10 ft \(3.0 m\), 5 Pins](#)
- [C4012148 - Adjustable Strain Pole, 14 ft \(4.2 m\), 5 Pins](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-E4011510P-SPEC-EN | REV 1/2024