



Tongue Type Strain Jack for Strain Poles, 12 in (0.3 m)

By Chance Lineman Tools & Equipment
Catalog # [E4011998P](#)

SCREW, JACK ASSY X 12", Acme Thread Strain Jack.



*Representative Image

Features

- 12"-Acme-thread Strain Jack

General

EU RoHS Indicator	No
Style	Accessories
UPC	096359084242

Dimensions

Dimensions	19.25 in x 2.5 in x 1 in
Height	1 in
Length	19.25 in
Length Metric	48.9 mm
Weight	6.0 lb
WeightMetric	2.7 kg
Width	2.5 in

Product Assets

[Literature - Transmission Project Tools and Equipment Checklist \(CENT_LTE_FRM_EN_00082\)](#)

Related Products

- [C4012147 - Adjustable Strain Pole, 10 ft \(3.0 m\), 5 Pins](#)
- [C4012146 - Adjustable Strain Pole, 8 ft \(2.4 m\), 5 Pins](#)
- [C4012145 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012144 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012215 - Adjustable Strain Pole, 12 ft \(3.6 m\), 5 Pins](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-E4011998P-SPEC-EN | REV 1/2024