



6ft. Temporary Screw-In Ground Rod

By Chance Lineman Tools & Equipment
Catalog # [G3370](#)

6ft. Temporary Screw-In Ground Rod



Features

- Screw-In Ground Rod provides a temporary ground when a system ground is not available
- When installed, the 6' spiraled ground rod develops less resistance than straight ground rods
- Actual effectiveness depends upon soil properties
- The reusable Ground Rod is copper clad
- The helix (spiral), handle and wing nut are bronze

General

Catalog Number	G3370
EU RoHS Indicator	No
UPC	096359038207

Dimensions

Weight	7.595 lb
--------	----------

Electrical Ratings

Current Rating	300 A
Fault Current - 15 Cycles	27000 A
Fault Current - 30 Cycles	20000 A

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Fault Current - ASTM Grade	ASTM Grade 3

Product Assets

- [Catalogs - Grounding Equipment](#)
- [Sales Drawings - SA_G3370](#)
- [Specifications - G3370](#)
- [Video - CHANCE Temporary Protective Grounding](#)
- [Video - CHANCE Temporary Protective Grounding](#)