

15kV Clear Rubber Glove Jumper Clamp Pair

By Chance Lineman Tools & Equipment
Catalog # [G4775](#)



35KV ORANGE RUBBER GLOVE JUMPER CLAMP PAIR

Features

- Designed and tested per ASTM F2321
- Maximum use voltage of 35kV
- Conductor range of #6 - 954 ACSR
- Robust orange body made from durable polyethylene plastic
- Handle length of 8-3/8" below handguard
- Includes 2 jumper clamps
- Used for bypassing work areas when equipment is under repair, upgrading lines, and making temporary or emergency repairs

General

EU RoHS Indicator No
Style 1 Pair of Clamps

Dimensions

Weight 3 lb
WeightMetric 1.3 kg

Electrical Ratings

Amperage Rating 400
Voltage - Maximum 35 kV
Voltage Rating 35 kV

Conductor Related

Cable Diameter Range #2, 4/0
Conductor Diameter (Main) - Maximum 954 ACSR 1.165 in
Conductor Diameter (Main) - Minimum 6 Copper 0.162 in

Logistics

Pallet Quantity 96

Product Assets

[Literature - CHANCE® Orange Jumper Clamps](#)



A Hubbell brand