

## Insulated Lever Type Wire Cutter For 2/0 Solid Copper Or 1/0 ACSR, 6 ft 6 in

By Chance Lineman Tools & Equipment  
Catalog # [H18716](#)



LEVER TYPE WIRE CUTTER-6FT 6IN- 1/0 ACSR, All cutters are assembled and mounted on Epoxiglas™ insulated poles. A solid fiberglass-reinforced operating rod insulates the linemen from the cutter head. The lever handle is coated with plastisol. The lever action gives the linemen added mechanical force to make clean cuts up to the maximum sizes.

### Features

- Three different cutter heads are available for linemen to use for cutting jumper wires, live conductors and tie wires
- All cutters are assembled and mounted on chance Epoxiglas™ insulated poles
- Solid fiberglass-reinforced operating rod insulates linemen from the cutter head
- Lever handle is coated with plastisol
- Lever action gives linemen added mechanical force to make clean cuts

### General

Catalog Number	H18716
Duty	Light
EU RoHS Indicator	No
Storage Bag Included?	P640-6 (Bag not included. Must be ordered separately.)

Type	Cutters
UPC	096359039280

### Dimensions

Length	78 in
Weight	6.8 lb
WeightMetric	3 kg

### Conductor Related

Conductor Size	2/0 Solid Copper or 1/0 ACSR
----------------	------------------------------

### Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)  
[Sales Drawings - Lever Type Wire Cutter](#)  
[Specifications - H18716](#)