



Insulated Lever Type Wire Cutter For 4/0 Stranded Copper Or 4/0 ACSR, 6 ft 7 in

By Chance Lineman Tools & Equipment
Catalog # [H18736](#)

LEVER TYPE WIRE CUTTER-6FT 7IN- 4/0 ACSR, All cutters are assembled and mounted on Epoxiglas™ insulated poles. A solid fiberglass-reinforced operating rod insulates the linemen from the cutter head. The lever handle is coated with plastisol. The lever action gives the linemen added mechanical force to make clean cuts up to the maximum sizes.

Features

- Three different cutter heads are available for linemen to use for cutting jumper wires, live conductors and tie wires
- All cutters are assembled and mounted on chance Epoxiglas™ insulated poles
- Solid fiberglass-reinforced operating rod insulates linemen from the cutter head
- Lever handle is coated with plastisol
- Lever action gives linemen added mechanical force to make clean cuts

General

Duty	Medium
EU RoHS Indicator	No
Storage Bag Included?	P640-6 (Bag not included. Must be ordered separately.)
Type	Cutters
UPC	096359039297

Dimensions

Length	78 in
Weight	9.5 lb
WeightMetric	4.3 kg

Conductor Related

Conductor Size	4/0 Stranded Copper or 4/0 ACSR
----------------	---------------------------------

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Sales Drawings - H1873-6_lever_type_wire_cutters](#)





A Hubbell brand