

## Single Range Analog Phasing Meter only to 40kV

By Chance Lineman Tools & Equipment  
Catalog # [H18767](#)



\*Representative Image

### Features

- Includes only Phasing Meter, Hook Probes, Case, and Instruction Manual (no Universal Poles)
- Two high-impedance components in fiberglass poles, each threaded for interchangeable probes
- 22-foot-long insulated flexible cable from voltmeter stores on reel on other pole
- Must be used with 2 Epoxiglas Insulating Universal Hotsticks (Not Included) of appropriate length

### General

Style	Analog Dial
UPC	096359039396

### Dimensions

Weight	23 lb
WeightMetric	10.4 kg

### Electrical Ratings

Withstand Voltage	40kV
-------------------	------

### Logistics

Pallet Quantity	25
Standard Package	1

### Product Assets

[Installation Manuals - CHANCE Phasing Testers Care and Operation Manual](#)  
[Installation Manuals - CHANCE® Analog Phasing Meters](#)  
[Video - CHANCE Meters and Instruments](#)