



Flexible Insulated Wrench, 6,3" Overall Length, W/ Flexible 1/2" Square Drive And Fixed 1/2" Square Drive

By Chance Lineman Tools & Equipment
Catalog # H18912



*Representative Image

Used for tightening nuts on hardware fittings on high-voltage lines

Features

- Epoxiglas™ Pole is tested per ASTM F711 AND IEC 60855
- Made using heavy duty 1.5" Diameter Epoxiglas Pole
- Overall Length is 6'3"
- 40 ft-lb torque rating
- Universal joint coil spring gives operator flexibility to control socket at various angles
- Spring is easily removed for lubrication
- Wrenches are made to fit any 1/2" square shank socket

General

EU RoHS Indicator	No
Storage Bag Included?	P643-6 (Bag not included. Must be ordered separately.)
Style	w/ Flexible 1/2" Sq. Plug & Fixed 1/2" Sq. Plug
Torque Rating	40 ft-lbs
UPC	096359039419

Dimensions

Dimensions	79.0 in x 4.38 in x 4.38 in
Height	4.38 in
Length	79.0 in
Length Metric	2006.6 mm
Weight	5.5 lb
Weight Metric	2.4 kg
Width	4.38 in

Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)
[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)<LineBreak/>



A proud member of the Hubbell Family.