

Flexible Insulated Wrench, 8 ft 3 in (2.5 m) with 1/2 in Flexible and Fixed Square Drives

By Chance Lineman Tools & Equipment
Catalog # [H18913](#)

Used for tightening nuts on hardware fittings on high-voltage lines

Features

- Epoxiglas™ Pole is tested per ASTM F711 AND IEC 60855
- Made using heavy duty 1.5" Diameter Epoxiglas Pole
- Overall Length is 8'3"
- 40 ft-lb torque rating
- Universal joint coil spring gives operator flexibility to control socket at various angles
- Spring is easily removed for lubrication
- Wrenches are made to fit any 1/2" square shank socket

General

Catalog Number	H18913
EU RoHS Indicator	No
Storage Bag Included?	P643-8 (Bag not included. Must be ordered separately.)
Style	w/ Flexible 1/2" Sq. Plug & Fixed 1/2" Sq. Plug
Torque Rating	40 ft-lbs
UPC	096359039426

Dimensions



*Representative Image

Dimensions	103.0 in x 4.38 in x 4.38 in
Dimensions Metric	261.6 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	103 in
Length Metric	261.6 mm
Weight	6.5 lb
Weight Metric	2.9 kg
Width	4.38 in
Width Metric	11.1 mm

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Product Assets

[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
[Instruction Manual](#)
[Sales Drawings - SA_H18913](#)
[Specifications - H18913](#)