



Flexible Insulated Wrench, 6 ft 3 in (1.9 m) with 1/2 in Flexible Square Drive and Universal Head

By Chance Lineman Tools & Equipment
Catalog # [H18915](#)



Used for tightening nuts on hardware fittings on high-voltage lines

Features

- Epoxiglas™ Pole is tested per ASTM F711 AND IEC 60855
- Made using heavy duty 1.5" Diameter Epoxiglas Pole
- Overall Length is 6'3"
- 40 ft-lb torque rating
- Universal joint coil spring gives operator flexibility to control socket at various angles
- Spring is easily removed for lubrication
- Wrenches are made to fit any 1/2" square shank socket
- Universal Head has a Hole Through Ferrule to allow for 5/8" Turning Rod to be used as a Torque Bar

General

Catalog Number	H18915
EU RoHS Indicator	No
Storage Bag Included?	P643-6 (Bag not included. Must be ordered separately.)
Style	w/ Flexible 1/2" Sq. Plug & Universal Head
Torque Rating	40 ft-lbs
UPC	096359039433

Dimensions

Dimensions	79.0 in x 4.38 in x 4.38 in
Dimensions Metric	2006.6 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	79 in
Length Metric	2006.6 mm
Weight	5.5 lb
Weight Metric	2.4 kg
Width	4.38 in
Width Metric	11.1 mm

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- [Catalogs - Insulated Hand Tools](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
- [Instruction Manual](#)
- [Sales Drawings - SA_H1891-5](#)
- [Specifications - H18915](#)



A Hubbell brand