



# Flexible Insulated Wrench, 8'3" Overall Length, W/ Flexible 1/2" Square Drive and Universal Head

By Chance Lineman Tools & Equipment  
Catalog # [H18916](#)



\*Representative Image

Used for tightening nuts on hardware fittings on high-voltage lines

## Features

- Epoxiglas™ Pole is tested per ASTM F711 AND IEC 60855
- Made using heavy duty 1.5" Diameter Epoxiglas Pole
- Overall Length is 8'3"
- 40 ft-lb torque rating Universal joint coil spring gives operator flexibility to control socket at various angles
- Spring is easily removed for lubrication
- Wrenches are made to fit any 1/2" square shank socket
- Universal Head has a Hole Through Ferrule to allow for 5/8" Turning Rod to be used as a Torque Bar

## General

EU RoHS Indicator	No
Storage Bag Included?	P643-8 (Bag not included. Must be ordered separately.)
Style	w/ Flexible 1/2" Sq. Plug & Universal Head
Torque Rating	40 ft-lbs
UPC	096359039440

## Dimensions

Dimensions	103.0 in x 4.38 in x 4.38 in
Height	4.38 in
Length	103.0 in
Length Metric	261.6 mm
Weight	9.0 lb
Weight Metric	4.0 kg
Width	4.38 in

## Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)  
[Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)  
[Sales Drawings - SA\\_H1891-5](#)



A proud member of the Hubbell Family.