

## Hinged Amertong 1.25 in (32 mm) X 8 ft 3 in (2.5 m)

By Chance Lineman Tools & Equipment  
Catalog # [H19788](#)

The Amertong can be adjusted at the collar to fit an ammeter. Plastic coated castings protect the finish on the meters and make a good secure gripping surface with easy handles and fiberglass operating rod provide maximum insulation.



### Features

- Tested per OSHA & ASTM F711
- Can be adjusted at collar to fit an ammeter
- Plastic-coated castings securely grip while protecting the meter's finish
- Fiberglass operating rod for maximum insulation

### General

EU RoHS Indicator	No
Storage Bag Included?	P640-8 (Bag not included. Must be ordered separately.)
Style	Hinged
UPC	096359039655

### Dimensions

Dimensions	96.0 in x 6.25 in x 6.25 in
Dimensions Metric	2438.4 mm x 15.9 mm x 15.9 mm
Height	6.25 in
Height Metric	15.9 mm
Length	96 in
Length Metric	2438.4 mm
Weight	5.5 lb
WeightMetric	2.4 kg
Width	6.25 in
WidthMetric	15.9 mm

### Logistics

Pallet Quantity	30
-----------------	----

### Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)