



# Extension for Epoxiglas Tree Trimmer - 1.25 in - 6 ft - With Male and Female Splices

By Chance Lineman Tools & Equipment  
Catalog # H2036

Splices telescope snugly and fasten securely to the splice fittings on the tool. Leaf-spring button lock is used on the Epoxiglas® models.



\*Representative Image

## Features

- Designed to cut up to 1½” diameter branches
- Useful around energized conductors or in hard-to-reach places
- Head features sharpened stationary and movable blades made of dropforged steel
- Rope and pulley arrangement gives operator a mechanical advantage of 3 to 1
- Example: A 10-lb. pull on rope will exert a 30-lb. force on the cutter head lever
- Ball bearing pulleys are employed for free operation
- Rope furnished with each tree trimmer is 25' long
- Accommodates a 6' extension on the basic tool
- The 18” long Universal Tool Fitting is provided with 25' of rope
- A Universal Pruning Saw can be added to the universal fitting on the side of the head mount
- Spliced extensions fasten securely to the tool with leaf spring button loc

## Dimensions

Length	72 in
Weight	3.4 lb
WeightMetric	1.5 kg

## Product Assets

[Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)<LineBreak/>

## General

Style	Extension - Male & Female Splice
Type	Cutters
UPC	096359039723



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-H2036-SPEC-EN | REV 1/2024