

Extension for Epoxiglas Tree Trimmer - 1.5 in - 8 ft - With Female Splice

By Chance Lineman Tools & Equipment
Catalog # [H2158](#)

Splices telescope snugly and fasten securely to the splice fittings on the tool. Leaf-spring button lock is used on the Epoxiglas®-models.

Features

- Designed to cut up to 1½" diameter branches
- Useful around energized conductors or in hard-to-reach places
- Head features sharpened stationary and movable blades made of dropforged steel
- Rope and pulley arrangement gives operator a mechanical advantage of 3 to 1
- Example: A 10-lb. pull on rope will exert a 30-lb. force on the cutter head lever
- Ball bearing pulleys are employed for free operation
- Rope furnished with each tree trimmer is 25' long
- Accommodates a 6' extension on the basic tool
- The 18" long Universal Tool Fitting is provided with 25' of rope
- A Universal Pruning Saw can be added to the universal fitting on the side of the head mount
- Spliced extensions fasten securely to the tool with leaf spring button loc

General

EU RoHS Indicator	No
Style	Extension - Female Splice
Type	Cutters
UPC	096359039846

Dimensions

Length	96 in
Weight	3.9 lb
WeightMetric	1.7 kg

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)





A Hubbell brand