



Disconnect Stick 1.25 in (32 mm) x 12 ft (3.6 m)

By Chance Lineman Tools & Equipment
Catalog # [H30469](#)

DISCONNECT STICK-1.25IN X 12FT -FG HEAD, Disconnect sticks provide insulation for linemen in opening and closing disconnect switches and cutouts. They are also used for installing and removing open-link fuse links. Poles are made of Epoxiglas™ NEMA-standard heads of cast bronze are of three types — switch head, disconnect head, or spliced disconnect head.

Features

- Provide insulation for linemen in opening and closing disconnect switches and cutouts
- Also used for installing and removing open-link fuse links
- Poles are made of Epoxiglas™
- NEMA-standard heads of cast bronze
- Available in three types: switch head, disconnect head, or spliced disconnect head
- Provides additional insulation required when bus and disconnect switch spacings are confined, as in indoor substations

General

Catalog Number	H30469
EU RoHS Indicator	No
Storage Bag Included?	P643-12 (Bag not included. Must be ordered separately.)
Style	1.25" (32 mm) Fiberglass Head
UPC	096359040132



*Representative Image

Dimensions

Dimensions	150.0 in x 4.38 in x 4.38 in
Dimensions Metric	3.8 m x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	150 in
Length Metric	3.8 m
Weight	7 lb
WeightMetric	3.2 kg
Width	4.38 in
WidthMetric	11.1 mm

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

- [Catalogs - Insulated Hand Tools](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
- [Instruction Manual](#)
- [Specifications - H30469](#)