

Spliced Disconnect Stick 1.25 in (32 mm) x 6 ft (1.8 m) and 1.5 in (38 mm) x 6 ft (1.8 m)

By Chance Lineman Tools & Equipment
Catalog # [H314612](#)

DISCONNECT STICK - SPLICED - 12FT(6+6), For convenience in transporting and/or where greater length is required, Spliced Disconnect Sticks are available. The splice is strong and rigid . . . easy to put together and easy to take apart. The taking-down feature of these sticks makes them especially handy to carry on line trucks or in tool trailers.

Features

- Provide insulation for linemen in opening and closing disconnect switches and cutouts
- Also used for installing and removing open-link fuse links
- Poles are made of Epoxiglas™
- NEMA-standard heads of cast bronze
- Available in three types: switch head, disconnect head, or spliced disconnect head
- For convenient transporting and/or when greater length is required
- Splice is strong and rigid - easy to assemble and disassemble
- Taking-down feature makes sticks easy to carry on line trucks and in tool trailers

General

| | |
|-----------------------|--|
| Catalog Number | H314612 |
| EU RoHS Indicator | No |
| Storage Bag Included? | P621-5 (Bag not included. Must be ordered separately.) |
| Style | Spliced Disconnect Stick |
| UPC | 096359040149 |



*Representative Image

Dimensions

| | |
|-------------------|-----------------------------|
| Dimensions | 82.0 in x 5.25 in x 5.25 in |
| Dimensions Metric | 2.0 m x 13.3 mm x 13.3 mm |
| Height | 5.25 in |
| Height Metric | 13.3 mm |
| Length | 82 in |
| Length Metric | 2 m |
| Weight | 6 lb |
| WeightMetric | 2.7 kg |
| Width | 5.25 in |
| WidthMetric | 13.3 mm |

Certifications And Compliance

| | |
|--------------------------|---|
| Buy America(n) Qualified | TAA Compliant (All status valid till December 2024) |
|--------------------------|---|

Product Assets

[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
[Instruction Manual](#)
[Specifications - H314612](#)