

Spliced Disconnect Stick 1.25 in (32 mm) x 8 ft (2.4 m) and 1.5 in (38 mm) x 10 ft (3.0 m)

By Chance Lineman Tools & Equipment
Catalog # [H314618](#)



*Representative Image

DISCONNECT STICK - SPLICED - 18FT(8+10), For convenience in transporting and/or where greater length is required, Spliced Disconnect Sticks are available. The splice is strong and rigid . . . easy to put together and easy to take apart. The taking-down feature of these sticks makes them especially handy to carry on line trucks or in tool trailers.

Features

- Provide insulation for linemen in opening and closing disconnect switches and cutouts
- Also used for installing and removing open-link fuse links
- Poles are made of Epoxiglas™
- NEMA-standard heads of cast bronze
- Available in three types: switch head, disconnect head, or spliced disconnect head
- For convenient transporting and/or when greater length is required
- Splice is strong and rigid - easy to assemble and disassemble
- Taking-down feature makes sticks easy to carry on line trucks and in tool trailers

General

Catalog Number	H314618
EU RoHS Indicator	No
Storage Bag Included?	P621-8 (Bag not included. Must be ordered separately.)
Style	Spliced Disconnect Stick
UPC	096359040163

Dimensions

Dimensions	127.0 in x 5.25 in x 5.25 in
Dimensions Metric	322.6 mm x 13.3 mm x 13.3 mm
Height	5.25 in
Height Metric	13.3 mm
Length	127 in
Length Metric	322.6 mm
Weight	8.3 lb
WeightMetric	3.7 kg
Width	5.25 in
WidthMetric	13.3 mm

Certifications And Compliance

Buy American Compliant Contact Manufacturer

Product Assets

[Catalogs - Insulated Hand Tools](#)
[Installation Manuals - CHANCE® Tools Manuals](#)
[Specifications - H314618](#)