



# Spliced Disconnect Stick, 1-1/4" x 10' and 1-1/2" x 10' 1"

By Chance Lineman Tools & Equipment  
Catalog # [H314620](#)



DISCONNECT STICK - SPLICED - 20FT(10+10), For convenience in transporting and/or where greater length is required, Spliced Disconnect Sticks are available. The splice is strong and rigid . . . easy to put together and easy to take apart. The taking-down feature of these sticks makes them especially handy to carry on line trucks or in tool trailers.

\*Representative Image

## Features

- Provide insulation for linemen in opening and closing disconnect switches and cutouts
- Also used for installing and removing open-link fuse links
- Poles are made of Epoxiglas™
- NEMA-standard heads of cast bronze
- Available in three types: switch head, disconnect head, or spliced disconnect head
- For convenient transporting and/or when greater length is required
- Splice is strong and rigid - easy to assemble and disassemble
- Taking-down feature makes sticks easy to carry on line trucks and in tool trailers

## Dimensions

Dimensions	140.0 in x 4.38 in x 4.38 in
Height	4.38 in
Length	140.0 in
Length Metric	355.6 mm
Weight	9.0 lb
WeightMetric	4.1 kg
Width	4.38 in

## Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)  
[Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)<LineBreak/>

## General

EU RoHS Indicator	No
Storage Bag Included?	P621-10 (Bag not included. Must be ordered separately.)
Style	Spliced Disconnect Stick
UPC	096359040170



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-H314620-SPEC-EN | REV 1/2024