



Suspension Link Stick, 114 in (2.9 m), 1.5 in (38 mm) dia.

By Chance Lineman Tools & Equipment
Catalog # [H4720114](#)

LINK STICK, SUSPENSION 11/2 X 9-1/2 FT, The Suspension Link Stick is designed for use on conductors from 1" to 2.5" diameter and can be used with various types of takeup devices at the structure end. The lip of the hook, actuated by an eye screw, swivels to accommodate various conductor sizes. The maximum load is 6,500 pounds.



*Representative Image

Features

- Snatch blocks hooked into butt ring to keep heandlines from dragging over tower structure, giving clearance to tools in transit
- Bronze mounting hooks are secured with bronze wing nuts on plated steel bolts
- Hook adjustment will fit tower angle from 1-3/4" x 1-3/4" up to 6" x 6"
- Maximum load for the gin is 500 lbs.

General

EU RoHS Indicator	No
Style	Link Stick
UPC	096359040798

Dimensions

Diameter	1.5 in
Dimension - L Length Overall mm	2,895 mm
Dimension - Length Overall inch	114 in
Dimensions	124 in x 7.25 in x 7.25 in
Height	7.25 in
Length	124 in
Length Metric	315.0 mm
Weight	30.0 lb
WeightMetric	13.6 kg
Width	7.25 in

Product Assets

[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)
[Literature - Transmission Project Tools and Equipment Checklist \(CENT_LTE_FRM_EN_00082\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-H4720114-SPEC-EN | REV 1/2024