

Suspension Link Stick, 84 in (2.1 m), 1.5 in (38 mm) dia.

By Chance Lineman Tools & Equipment
Catalog # [H472084](#)



LINK STICK, SUSPENSION 1 1/2 X 7 FT, The Suspension Link Stick is designed for use on conductors from 1" to 2.5" diameter and can be used with various types of takeup devices at the structure end. The lip of the hook, actuated by an eye screw, swivels to accommodate various conductor sizes. The maximum load is 6,500 pounds.

Features

- Snatch blocks hooked into butt ring to keep heandlines from dragging over tower structure, giving clearance to tools in transit
- Bronze mounting hooks are secured with bronze wing nuts on plated steel bolts
- Hook adjustment will fit tower angle from 1-3/4" x 1-3/4" up to 6" x 6"
- Maximum load for the gin is 500 lbs.

General

Catalog Number	H472084
EU RoHS Indicator	No
Style	Link Stick
UPC	096359040804

Dimensions

Diameter	1.5 in
Diameter - Metric	0 m
Dimension - L Length Overall	2.1 m
mm	

Dimension - Length Overall	84 in
inch	
Dimensions	93 in x 7.25 in x 7.25 in
Dimensions Metric	236.2 mm x 18.4 mm x 18.4 mm
Height	7.25 in
Height Metric	18.4 mm
Length	93 in
Length Metric	236.2 mm
Weight	27.5 lb
WeightMetric	12.4 kg
Width	7.25 in
WidthMetric	18.4 mm

Certifications And Compliance

Buy America(n) Qualified Contact Manufacturer

Product Assets

[Catalogs - Transmission Tools](#)
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
[Instruction Manual](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)
[Specifications - H472084](#)