



Clevis Type Strain Jack for Strain Poles, 24 in (0.6 m)

By Chance Lineman Tools & Equipment
Catalog # H47853

Acme Thread Strain Jack.



*Representative Image

Features

- Strain Jack (24" Long) Clevis Type

General

EU RoHS Indicator	No
Style	Accessories
UPC	096359040897

Dimensions

Dimensions	32 in x 3 in x 3 in
Height	3 in
Length	32 in
Length Metric	81.3 mm
Weight	7.0 lb
WeightMetric	3.1 kg
Width	3 in

Product Assets

[Literature - Transmission Project Tools and Equipment Checklist \(CENT_LTE_FRM_EN_00082\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-H47853-SPEC-EN | REV 1/2024