



Epoxiglas™ Manhole Ladder, 12 ft 1 in length

By Chance Lineman Tools & Equipment
Catalog # H4903M12



*Representative Image

LADDER, MANHOLE 1.5IN RAILS X 12FT LONG, Service Ladders of Epoxiglas offer greater safety when working around energized lines. Because they are much lighter than comparable wood ladders they are easier to transport. Spacing between side rails and rung spacings are in accordance with the specifications of the largest central station and telephone companies. Side rails of 1 1/2"-diameter Epoxiglas are plastic-covered at the top for cushioning. Rubber feet are supplied on bottom end. Rungs are of 1316"-diameter glass fiber.

Features

- Offer greater safety when working around energized lines
- Easier to transport - much lighter than comparable wood ladders
- Spacing between side rails and rungs meets largest central station and telephone company specifications
- Side rails of 1-1/2"-dia. Epoxiglas are plastic-covered at top for cushioning
- Rubber feet are supplied on bottom end
- Rubber feet are supplied on bottom end

General

EU RoHS Indicator	No
Style	Service Ladder
UPC	096359041054

Dimensions

Dimensions	12 ft x 27 in x 252 in
Height	252 in
Length	12 ft
Length Metric	3.6 m
Side Rail Space	12.0 in, 30.4 cm
Weight	148.0 lb
WeightMetric	67.1 kg
Width	27 in

Product Assets

[Catalogs - Ladders & Platforms \(2350\)](#)
[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)<LineBreak/>
[Literature - Transmission Project Tools and Equipment Checklist \(CENT_LTE_FRM_EN_00082\)](#)



A proud member of the Hubbell Family.