



## Standard Platform, 42 in with Fixed Pole Mount

By Chance Lineman Tools & Equipment  
Catalog # [H49644W](#)

Designed to provide a convenient workstation on an aerial structure. Bare section near mounting end helps reduce moisture accumulation in inclement weather and provides area between working surface and mount fittings that can be cleaned of dirt and moisture when necessary.



### Features

- Furnished Fixed Pole Mount includes chain binder and adjusting wheel
- Optional Epoxiglas Tripod and Pivot Base sold separately
- IMPORTANT: Rails and Tripods are not suited for use as a fall restraint device
- 500 lbs. Maximum Load Rating
- Three strips of 2 in (51 mm) non-skid tape extend the length of platform surface

### General

EU RoHS Indicator	No
Strength Rating - Ultimate	500 lb
Style	Standard Aerial Platform
UPC	096359041351

### Dimensions

Dimensions	52.56 in x 12.13 in x 6.19 in
Height	6.19 in
Length	52.56 in
Length Metric	133.5 mm
Weight	48.0 lb
WeightMetric	21.7 kg
Width	12.13 in

### Product Assets

[Catalogs - Ladders & Platforms \(2350\)](#)  
[Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)<LineBreak/>  
[Installation Manuals - Instructions for CHANCE® Temporary Work Platform \(TD09188E1019\)](#)  
[Video - CHANCE Installation and Safety guide for Platforms \(VI09070E1119\)](#)

### Related Products

[T4021195 - Tripod for 42" or 4' Standard Platforms](#)  
[C4021164 - Pivot Base for 42 in or 4ft Platforms](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-H49644W-SPEC-EN | REV 1/2024