



Standard Platform, 6 ft with Fixed Pole Mount

By Chance Lineman Tools & Equipment

Catalog # [H49646W](#)

Designed to provide a convenient workstation on an aerial structure. Bare section near mounting end helps reduce moisture accumulation in inclement weather and provides area between working surface and mount fittings that can be cleaned of dirt and moisture when necessary.

Features

- Furnished Fixed Pole Mount includes chain binder and adjusting wheel
- Optional Epoxiglas Tripod and Pivot Base sold separately
- IMPORTANT: Rails and Tripods are not suited for use as a fall restraint device
- 500 lbs. Maximum Load Rating
- Three strips of 2 in (51 mm) non-skid tape extend the length of platform surface

General

Catalog Number	H49646W
EU RoHS Indicator	No
Strength Rating - Ultimate	500 lb
Style	Standard Aerial Platform
UPC	096359041375

Dimensions



Dimensions	72 in x 12.13 in x 6.19 in
Dimensions Metric	182.9 mm x 30.8 mm x 15.7 mm
Height	6.19 in
Height Metric	15.7 mm
Length	72 in
Length Metric	182.9 mm
Weight	63 lb
WeightMetric	28.5 kg
Width	12.13 in
WidthMetric	30.8 mm

Product Assets

- [Installation Manuals - CHANCE® Tools Manuals](#)
- [Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)
- [Specifications - H49646W](#)
- [Video - CHANCE Installation and Safety guide for Platforms](#)