

Standard Platform, 8 ft with Fixed Pole Mount

By Chance Lineman Tools & Equipment
Catalog # [H49648W](#)

Designed to provide a convenient workstation on an aerial structure. Bare section near mounting end helps reduce moisture accumulation in inclement weather and provides area between working surface and mount fittings that can be cleaned of dirt and moisture when necessary.

Features

- Furnished Fixed Pole Mount includes chain binder and adjusting wheel
- Optional Epoxiglas Tripod and Pivot Base sold separately
- IMPORTANT: Rails and Tripods are not suited for use as a fall restraint device
- 500 lbs. Maximum Load Rating
- Three strips of 2 in (51 mm) non-skid tape extend the length of platform surface

General

Catalog Number	H49648W
EU RoHS Indicator	No
Strength Rating - Ultimate	500 lb
Style	Standard Aerial Platform
UPC	096359041382

Dimensions

Dimensions	101 in x 15 in x 11.5 in
Dimensions Metric	256.5 mm x 38.1 mm x 29.2 mm



Height	11.5 in
Height Metric	29.2 mm
Length	101 in
Length Metric	256.5 mm
Weight	76 lb
WeightMetric	34.4 kg
Width	15 in
WidthMetric	38.1 mm

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

[Catalogs - Ladders & Platforms](#)
[Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)
[Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool Instruction Manual](#)
[Specifications - H49648W](#)
[Video - CHANCE Installation and Safety guide for Platforms](#)