

Positive Grip Clamp Stick 1.25 in (32 mm) X 8 ft (2.4 m) with Regular Length Head

By Chance Lineman Tools & Equipment
Catalog # [HG30302](#)



POSITIVE GRIP CLAMPSTICK 8FT6IN REGHEAD, The Epoxiglas Positive Grip Clampstick is made for use on eyescrew grounding or hot line clamps. It can be mounted on the line and tightened at angles up to 30°. Fittings are aluminum and bronze. To install clamp, align locking ring with slot in housing- place eye of clamp into housing. Holding locking ring and clamp in one hand, rotate pole clockwise to trap eye. To remove clamp, engage locking ring on clamp body and rotate pole counter-clockwise to trap eye. The butt end of the tool is equipped with a combination tool hanger and universal head.

Features

- Tested per OSHA & ASTM F711
- For use on eyescrew grounding or hot line clamps
- Can be mounted on the line and tightened at up to 30° angles
- Aluminum and bronze fittings

General

EU RoHS Indicator	No
Storage Bag Included?	P621-8 (Bag not included. Must be ordered separately.)
Style	Standard Length Head
UPC	096359038696

Dimensions

Dimensions	102 in x 3.38 in x 3.38 in
Dimensions Metric	259.1 mm x 8.6 mm x 8.6 mm
Height	3.38 in
Height Metric	8.6 mm
Length	102 in
Length Metric	259.1 mm
Weight	5.33 lb
WeightMetric	2.4 kg
Width	3.38 in
WidthMetric	8.6 mm

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand