

Mounted Duckbill Ground Clamp 6', Type II-Class B-Grade 4, 1.162" Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # [HG37061](#)

Mounted Duckbill Ground Clamp 6', Type II-Class B-Grade 4,
1.162" Jaw Opening

Features

- Mounted Duckbill Ground Clamp
- Continuous Current 400A
- Fault Current 34kA for 15 cycles or 25kA for 30 cycles
- Main Line Range Max. 566kcmil CU or 900kcmil ACSR (1.162")
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type II, Class A, Grade 4
- Jaws Smooth
- Ferrule Plain-Plug

General

Catalog Number	HG37061
EU RoHS Indicator	No
Eye Screw/T-Handle	300 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Hotstick
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
Thread Type	Plain Plug
Torque Rating	300 in-lbs



UPC 096359038757

Dimensions

Jaw Opening Size - Maximum	1.162 in
Jaw Opening Size - Minimum	.162 in
Length	6 in
Weight	7.84 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Fault Current - ASTM Grade	ASTM Grade 5

Product Assets

[Catalogs - Grounding Equipment](#)
[Specifications - HG37061](#)